

Test Report

Report No.: GZEE231200489331
Amendment 02 Date: 2026-03-31

The following sample(s) was/were submitted and identified on behalf of the client as:

Applicant: Shenzhen Chengxing Electronic Technology Co., Ltd.
Room 705 - 709, Nanguang Building, No.1004 Huafu Road, Futian District, Shenzhen, China

Manufacturer: XINGLIGHT
Room 705 - 709, Nanguang Building, No.1004 Huafu Road, Futian District, Shenzhen, China

Factory: Same as manufacturer

Testing location/address: SGS-CSTC Standards Technical Services Co., Ltd. Guangzhou Branch
198 Kezhu Road, Science City, Economic & Technology Development Area, Guangzhou, Guangdong, China

Standard(s): IEC 62471:2006
Photobiological safety of lamps and lamp systems

Test item description: LED

Trade Mark/Brand: XINGLIGHT

Model/Type reference: XL-2835UWC, 3528, 3014, 6028, 5730, 3030, 3020, 3433, 020, 335, 5050, 3535, 215, 2121, 4020, 6070, 7060, 4014, 8080, 6048, 2020, 5630, 2720, 1808, 2214, 4040, 3036, 2520, 3838

Ratings: DC 50 - 60 mA, 1,8 - 3,4 V

Test result: The test sample belongs to RG0

Remark: Throughout this report a comma is used as the decimal separator.

Alex Tan
Reviewer
E&E Safety Laboratory

Junny Huang
Project Engineer



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.
Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

SGS-CSTC Standards Technical Services Co., Ltd. | No.198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 | t (86-20) 82155555 | www.sgs.com.cn
Guangzhou Branch | E&E Laboratory. | 中国·广东·广州高新技术产业开发区科学城科珠路198号 | 邮编: 510663 | t (86-20) 82155555 | sgs.china@sgs.com

Member of the SGS Group (SGS SA)

Test Report

Report No.: GZEE231200489331
Amendment 02 Date: 2026-03-31

Copy of marking plate N/A
Summary of testing: The test model XL-2835UWC was tested under 60 mA DC. It belongs to RG0 according to IEC 62471:2006.
Use of uncertainty of measurement for decisions on conformity (decision rule) : No decision rule is specified by the standard, when comparing the measurement result with the applicable limit according to the specification in that standard. The decisions on conformity are made without applying the measurement uncertainty ("simple acceptance" decision rule, previously known as "accuracy method").
Test item particulars : Tested lamp..... : <input checked="" type="checkbox"/> continuous wave lamps <input type="checkbox"/> pulsed lamps Tested lamp system : — Lamp cap : — Bulb..... : — Seasoning of lamps according IEC standard ..: 0 h
Testing Date of receipt of test item : 2023-12-19 Date (s) of performance of tests : 2023-12-19 to 2023-12-29
General product information: The product can emit white light when powered. All models used the same die and they only differ in the package size. XL-2835UWC was selected to conduct the full test. Revision History: 1 st Revision Summary: Based on and superseded the original summary report GZEE231200489331 dated 2024-01-08. This revision included the below changes: - Updated the Manufacturer and factory information on page 1. - Add new models 2520 and 3838, they were same as model XL-2835UWC except package size. After reviewed, no additional test was considered necessary. 2 nd Revision Summary: Based on and superseded the original summary report GZEE231200489331 Amendment 01 dated 2025-04-03. This revision included the below changes: - Updated the applicant, manufacturer, factory information and Rating on page 1, after reviewed, no additional test was considered necessary.



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.
Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com
 No.198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 t (86-20) 82155555 www.sgsgroup.com.cn
 中国·广东·广州高新技术产业开发区科学城科珠路198号 邮编: 510663 t (86-20) 82155555 sgs.china@sgs.com

Member of the SGS Group (SGS SA)

1 Measurement conditions

Seasoning of lamps shall be done as stated in the appropriate IEC lamp standard. The seasoning time for fluorescent or High Intensity Discharge (HID) types is typically 100 h, 0 h for LED lamp.

The sample was measured in a dark room with ambient temperature $25^{\circ}\text{C} \pm 1^{\circ}\text{C}$ & Max. 65 % Rh.

Measure distance:

For lamps intended for general lighting service (GLS), the hazard values shall be reported as either irradiance or radiance values at a distance which produces an illuminance of 500 lux, but not at a distance less than 200 mm;

For all other light sources, including pulsed lamp sources, the hazard values shall be reported at a distance of 200 mm.

2 Measurement procedure

2.1 Irradiance measurements

The input aperture diameter was 7 mm Min. to 50 mm Max.

The measurement shall be made in that position of the beam giving the maximum reading. The instrument shall be calibrated to read in absolute incident radiant power per unit receiving area. Summary of the ELs see table 5.4




Figure 5.1 Schematic - Irradiance measurements.



SGS-CT Standards Technical Services Co., Ltd.
Guangzhou Branch IEC Laboratory

Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

No.198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 t (86-20) 82155555 www.sgs.com.cn
中国·广东·广州高新技术产业开发区科学城科珠路198号 邮编: 510663 t (86-20) 82155555 sgs.china@sgs.com

Member of the SGS Group (SGS SA)

2.2 Radiance measurements - Standard method

As with irradiance measurements, the minimum aperture stop diameter D , as shown in Figure 5.2, corresponds to a 7 mm pupil diameter.

The instrument shall be calibrated to read in absolute incident radiant power per unit receiving area and per unit solid angle of acceptance averaged over the field of view (FOV) of the instrument. Summary of the ELs see table 5.5.




Figure 5.2 Example of an imaging device for radiance measurements.

2.3 Measurement of source size

The determination of α , the angle subtended by a source, requires the determination of the 50% emission points of the source.

Due to physical limitations of the eye, the value for α_{min} is 0,0017 radian & α_{max} is 0,1 radian for all retinal hazards in this standard.

The angular subtense of an oblong source shall be determined by the arithmetic mean of the maximum and minimum angular dimensions of the source:

$$\alpha = (a+b)/2r$$

Any angular dimension larger than α_{max} shall be limited to α_{max} and any angular dimension smaller than α_{min} shall be limited to α_{min} , prior to the determination of the arithmetic mean.

2.4 Pulse width measurement for pulsed sources (only for Pulse lamp)

The determination of Δt , the nominal pulse duration of a source, requires the determination of the time during which the emission is > 50% of its peak value.



SGS-CSI Standards Technical Services Co., Ltd.
Guangzhou Branch, CMAA, CNAS, EEC Laboratory

Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

No.198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 t (86-20) 82155555 www.sgsgroup.com.cn
中国·广东·广州高新技术产业开发区科学城科珠路198号 邮编: 510663 t (86-20) 82155555 sgs.china@sgs.com

Member of the SGS Group (SGS SA)

Table 5.4a Summary of the ELs for the surface of the skin or cornea (irradiance based values) for IEC 62471						
Hazard Name	Relevant equation	Wavelength range nm	Exposure duration sec	Limiting aperture rad (deg)	EL in terms of constant irradiance $W \cdot m^{-2}$	Risk group exposure duration sec
Actinic UV skin & eye	$E_S = \sum E_\lambda \cdot S(\lambda) \cdot \Delta\lambda$	200 – 400	< 30000	1,4 (80)	30/t	RG2: t ≤ 1000 RG1: t ≤ 10000 RG0: t ≤ 30000
Eye UV-A	$E_{UVA} = \sum E_\lambda \cdot \Delta\lambda$	315 – 400	≤1000 >1000	1,4 (80)	10000/t 10	RG2: t ≤ 100 RG1: t ≤ 300 RG0: t ≤ 1000
Blue-light small source	$E_B = \sum E_\lambda \cdot B(\lambda) \cdot \Delta\lambda$	300 – 700	≤100 >100	< 0,011	100/t 1,0	RG2: t ≤ 100 RG0/1: t > 100
Eye IR	$E_{IR} = \sum E_\lambda \cdot \Delta\lambda$	780 – 3000	≤1000 >1000	1,4 (80)	18000/t ^{0.75} 100	RG2: t ≤ 10 RG1: t ≤ 100 RG0: t ≤ 1000
Skin thermal	$E_H = \sum E_\lambda \cdot \Delta\lambda$	380 – 3000	< 10	2π sr	20000/t ^{0.75}	—

Table 5.5a Summary of the ELs for the retina (radiance based values) for IEC 62471						
Hazard Name	Relevant equation	Wavelength range nm	Exposure duration sec	Field of view radians	EL in terms of constant radiance $W \cdot m^{-2} \cdot sr^{-1}$	Risk group exposure duration sec
Blue light	$L_B = \sum L_\lambda \cdot B(\lambda) \cdot \Delta\lambda$	300 – 700	0,25 – 10 10-100 100-10000 ≥ 10000	0,011·√(t/10) 0,011 0,0011·√t 0,1	10 ⁶ /t 10 ⁶ /t 10 ⁶ /t 100	RG2: t ≤ 0,25 RG1: t ≤ 100 RG0: t ≤ 10000
Retinal thermal	$L_R = \sum L_\lambda \cdot R(\lambda) \cdot \Delta\lambda$	380 – 1400	< 0,25 0,25 – 10	0,0017 0,011·√(t/10)	50000/(α·t ^{0.25}) 50000/(α·t ^{0.25})	RG2: t ≤ 0,25 RG0/1: t ≤ 10
Retinal thermal (weak visual stimulus)	$L_{IR} = \sum L_\lambda \cdot R(\lambda) \cdot \Delta\lambda$	780 – 1400	> 10	0,011	6000/α	RG2: t ≤ 10 RG1: t ≤ 100 RG0: t ≤ 1000



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

SGS-CSI Standards Technical Services Co., Ltd. No.198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 t (86-20) 82155555 www.sgsgroup.com.cn
Guangzhou Branch of SGS-CSI EEC Laboratory. 中国·广东·广州高新技术产业开发区科学城科珠路198号 邮编: 510663 t (86-20) 82155555 sgs.china@sgs.com

Member of the SGS Group (SGS SA)

3 Emission limit & Test result:

Table 6.1a Emission limits for risk groups of continuous wave lamps (IEC 62471)									
Risk	Action spectrum	Symbol	Units	Emission Measurement					
				Exempt		Low risk		Mod risk	
				Limit	Result	Limit	Result	Limit	Result
Actinic UV	SUV(λ)	E_s	$W \cdot m^{-2}$	0,001	0	0,003	—	0,03	—
Near UV	—	E_{UVA}	$W \cdot m^{-2}$	10	0	33	—	100	—
Blue light	B(λ)	L_B	$W \cdot m^{-2} \cdot sr^{-1}$	100	—	10000	—	4000000	—
Blue light, small source	B(λ)	E_B	$W \cdot m^{-2}$	1,0*	$1,54 \times 10^{-1}$	1,0	—	400	—
Retinal thermal	R(λ)	L_R	$W \cdot m^{-2} \cdot sr^{-1}$	$3,59 \times 10^6$ (28000/ α)	$1,15 \times 10^4$	$3,59 \times 10^6$ (28000/ α)	—	$9,10 \times 10^6$ (71000/ α)	—
Retinal thermal, weak visual stimulus**	R(λ)	L_{IR}	$W \cdot m^{-2} \cdot sr^{-1}$	$7,69 \times 10^5$ (6000/ α)	—	$7,69 \times 10^5$ (6000/ α)	—	$7,69 \times 10^5$ (6000/ α)	—
IR radiation, eye	—	E_{IR}	$W \cdot m^{-2}$	100	$8,27 \times 10^{-4}$	570	120	3200	—
Skin thermal	—	E_H	$W \cdot m^{-2}$	$3556,6$ (20000/ $t^{0.75}$)	$4,42 \times 10^{-1}$	—	—	—	—
Angular subtense of apparent source $\alpha = 0,0078$ rad									
Only for pulse source: Frequency: -- Hz, Pulse duration: -- s, Constant duty factor: -- %									
* Small source defined as one with $\alpha < 0,011$ radian. Averaging field of view at 10000 s is 0,1 radian.									
** Involves evaluation of non-GLS source									



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

SGS-CSI Standards Technical Services Co., Ltd. No. 198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 t (86-20) 82155555 www.sgsgroup.com.cn
Guangzhou Branch of SGS-CSI EEC Laboratory. 中国·广东·广州高新技术产业开发区科学城科珠路198号 邮编: 510663 t (86-20) 82155555 sgs.china@sgs.com

Member of the SGS Group (SGS SA)

Test Report


Report No.: GZEE231200489331
Amendment 02 Date: 2026-03-31

Photo documentation:

Details of: View of model XL-2835UWC

View:

- general
- front
- rear
- right
- left
- top
- bottom



--- End of Report ---



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <https://www.sgs.com/en/Terms-and-Conditions>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

SGS-CS Standards Technical Services Co., Ltd. No.198, Kezhu Road, Science City, Economic & Technological Development Area, Guangzhou, Guangdong, China 510663 t (86-20) 82155555 www.sgsgroup.com.cn
Guangzhou Branch of SGS EEC Laboratory. 中国·广东·广州高新技术产业开发区科学城科珠路198号 邮编: 510663 t (86-20) 82155555 sgs.china@sgs.com

Member of the SGS Group (SGS SA)